

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191410024

Status:

Active

Overview:

Description:

Krimptite Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19141
Crimp Quality Equipment	Yes
Overview	solderless_terminals
Product Name	Krimptite
Type	Spade
UPC	800755086423
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.488/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25-1.50
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	AA-135-10
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	AACD10303-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19141 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm² Crimp Head for the AT-200 Pneumatic Hand Tool	640030100
ServiceGrade Hand Crimp Tool - Ratchet	640070100
	640160038

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19141-0024](#)