

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640141](#)
Status: **Active**
Overview: [Perma-Seal Terminals](#)
Description: Perma-Seal Hook Tongue Terminal for 14-16 AWG Wire, Stud Size 6 (M3.5)

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19164](#)
 Crimp Quality Equipment Yes
 Overview [Perma-Seal Terminals](#)
 Product Name Perma-Seal
 Type Hook
 UPC 800753114234

Physical

Barrel Type Closed
 Insulation NiAc
 Material - Plating Mating Tin
 Net Weight 1.187/g
 Packaging Type Bag
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Stud Size 6 (M3.5)
 Wire Insulation Diameter 5.97mm
 Wire Size AWG 14, 16
 Wire Size mm² 1.23-1.94

Material Info

Engineering Number SB-219-06

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19164-002-001



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19164 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)	640017400
Power Crimp Tool Head for Terminals 10-22 AWG Wire	640057400
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640160041

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19164-0141](#)