

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191930233

Status:

Active

Overview:

VersaKrimp Terminals and Splices

Description:

VersaKrimp Ring Tongue Terminal for 6 AWG Wire

Documents:


Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19193
Crimp Quality Equipment	Yes
Overview	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Type	Ring
UPC	800755050806
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	5.674/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	5/8" (M16)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	6
Material Info	
Engineering Number	E-358-58
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19193-005-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19193 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Manual Putt Pump Hydraulic System, Die set required	192860117
Die Set (large) for the HHLS Hydraulic Crimper	192900004
Hydraulic Dieless Crimping Tool	638161700
PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals	640013900
Square “DIN” style dies for 6 AWG	640037770

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19193-0233](#)