

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191990010](#)
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp Window Butt Connector for 14-16 AWG Wire, Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Splices](#)
Series [19199](#)
Comments Mil Spec M7928/5-4
Crimp Quality Equipment Yes
Overview [Splices](#)
Product Name Avikrimp, Butt - Window
UPC 800753046832

Physical
Barrel Type Closed
Color - Resin Blue
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 2.192/g
Packaging Type Adhesive Tape on Reel
Temperature Range - Operating -55° to +105°C
Wire Insulation Diameter 4.34mm
Wire Size AWG 14, 16
Wire Size mm² 1.00-2.50

Electrical
Voltage - Maximum 300V

Material Info
Engineering Number WB-841T

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-015-001
Sales Drawing SD-19199-003-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS Not Relevant ELV Not Relevant RoHS Phthalates Not Contained
--	---

Search Parts in this Series
[19199 Series](#)

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880118

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19199-0010](#)