

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192000013](#)
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp Seamless Butt Splice for 14-16 AWG Wire, Super Duty

Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-19406-001-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Splices
Series [19200](#)
Comments Blue
Crimp Quality Equipment Yes
Overview [Splices](#)
Product Name Avikrimp
UPC 756054494226

Physical
Barrel Type Closed
Color - Resin Blue
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 736.000/g
Packaging Type Bag
Temperature Range - Operating 105°C
Wire Insulation Diameter 4.29mm
Wire Size AWG 14, 16

Electrical
Voltage - Maximum 600V

Material Info
Engineering Number BS-831 BAG100

Reference - Drawing Numbers
[Packaging Specification](#) PK-19406-001-001
[Product Specification](#) PS-19902-011-001
[Sales Drawing](#) SD-19200-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/108/2014 (17 Dec 2014)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19200 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19200-0013](#)