

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192020039

Status:

Active

Overview:

[Splices](#)

Description:

Funnel Entry Butt Splice for 10-12 AWG Wire

Documents:


[Drawing \(PDF\)](#)

[Product Specification PS-19902-011-001 \(PDF\)](#)

[Product Specification PS-19902-013-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Splices
Series	19202
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Butt - Funnel Entry
UPC	800753048003
Physical	
Barrel Type	Closed
Color - Resin	Yellow
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.359/g
Packaging Type	Adhesive Tape on Reel
Wire Insulation Diameter	6.65mm max. Funnel End, 7.01mm max.
Wire Size AWG	10, 12
Material Info	
Engineering Number	C-946-DK
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19202-002-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19202](#) Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Hand Crimp Tool	640015000
Crimp Head for the AT-200 Pneumatic Hand Tool	640055000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19202-0039](#)