

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192030113

Status:

Active

Overview:

High-Temperature Temp Terms Terminals and Splices

Description:

Krimptite Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)

Documents:	
3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19203
Comments	1200° F (649° C)
Crimp Quality Equipment	Yes
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite, Temp-Terms
Type	Ring
UPC	800755059533
Physical	
Barrel Type	Closed
Insulation	None
Net Weight	1.326/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Size AWG	10, 12
Wire Size mm²	4.00-6.00
Material Info	
Engineering Number	C-U-128-10
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19069-020-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19203 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 08/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0113](#)