

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192030389

Status:

Active

Overview:

High-Temperature Temp Terms Terminals and Splices

Description:

Krimptite Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)

Documents:

Drawing (PDF)

Product Specification 194130096-000 (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19203
Crimp Quality Equipment	Yes
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite
Type	Ring
UPC	822348424788
Physical	
Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Net Weight	1.180/g
Packaging Type	Carton
Stud Size	10 (M5)
Temperature Range - Operating	483°C
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.70mm max.
Wire Size AWG	10, 12
Wire Size mm²	4.00-6.00
Material Info	
Reference - Drawing Numbers	
Product Specification	194130096-000, PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19203-018



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19203 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 07/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0389](#)