

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192150018

Status:

Active

Overview:

Splices

Description:

VersaKrimp Butt Splice for 14-16 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

|                                |                                    |
|--------------------------------|------------------------------------|
| Agency Certification           |                                    |
| CSA                            | LR18689                            |
| UL                             | E32244                             |
| General                        |                                    |
| Product Family                 | Splices                            |
| Series                         | 19215                              |
| Crimp Quality Equipment        | Yes                                |
| Overview                       | Splices                            |
| Product Name                   | Butt, VersaKrimp                   |
| UPC                            | 800755062458                       |
| Physical                       |                                    |
| Barrel Type                    | Closed - Brazed                    |
| Insulation                     | None                               |
| Material - Metal               | Copper                             |
| Material - Plating Mating      | Tin                                |
| Material - Plating Termination | Tin                                |
| Net Weight                     | 1.094/g                            |
| Packaging Type                 | Bag                                |
| Wire Size AWG                  | 14, 16                             |
| Solder Process Data            |                                    |
| Lead-freeProcess Capability    | N/A                                |
| Material Info                  |                                    |
| Engineering Number             | BS-331                             |
| Reference - Drawing Numbers    |                                    |
| Product Specification          | PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing                  | SD-19215-002-001                   |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19215 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

| Global                                                                                                     |           |
|------------------------------------------------------------------------------------------------------------|-----------|
| Description                                                                                                | Product # |
| PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm² | 640030100 |
| Crimp Head for the AT-200 Pneumatic Hand Tool                                                              | 640070100 |
| ServiceGrade Hand Crimp Tool - Ratchet                                                                     | 640160038 |

This document was generated on 10/01/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19215-0018](#)