

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192880085

Status:

Active

Overview:

Application Tooling

Description:

ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207126
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200 , 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ETC
Tool Type	Crimp Module
UPC	800753109445
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number

ATP-B-520

Reference - Drawing Numbers

Application Tooling Documents

192880085-001, ATS-TOOLING-ID-ATP-0, TM-192280498-001, TM-192280498SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001,

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

207126 Series

Use With

Molex Crimp Tape Module 640162000 used with Molex TM-3000: 638017200 , 638017300 , Molex TM-4000: 638017600 , Molex ATP-301 Press: 192280030 and Molex ATP-101 style presses.

Application Tooling Description	FAQ Product #
Avikrimp Quick Disconnect, Male, for 14-16 (2.00-1.30mm²), Mylar Tape, Tab 6.35 x 0.81mm	190010007
Avikrimp Quick Disconnect, Male, for 14-16 (2.00-1.30mm²), Mylar Tape, Tab 4.75 x 0.51mm	190010009
InsulKrimp Fully Insulated Quick Disconnect, Male,	190230014

TM-640160065TH-001, TM-640160065TW-001,
TM-640160065VN-001

for 14-16 AWG
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 6.35
x 0.81mm
Avikrimp Quick 190250009
Disconnect, Male,
for 14-16 AWG
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 4.75
x 0.51mm
Avikrimp Quick 190250010
Disconnect,
Male, for 14-16
(2.00-1.30mm²) Wire,
Mylar Tape, Tab 6.35
x 0.81mm
Avikrimp Snap Plug, 190350008
for 14-16 AWG
Wire, Mylar Tape,
24.08mm Length
Avikrimp Snap Plug, 190350012
for 14-16 AWG
Wire, Mylar Tape,
22.55mm Length
Avikrimp Snap Plug, 190360007
for 14-16 AWG
Wire, Mylar Tape,
24.31mm Length
Avikrimp Snap Plug, 190360009
for 14-16 AWG
Wire, Mylar Tape,
22.78mm Length

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19288-0085](#)