

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0193240001

Status:

Active

Overview:

Description:

Avikrimp Metric Ring Terminal for Stud Size 4 (M2.6), Insulated Barrel

Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19324
Crimp Quality Equipment	Yes
Overview	metric_ring_terminals
Product Name	Avikrimp
Type	Ring
UPC	887191290010
Physical	
Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.781/g
Packaging Type	Bag
Stud Size	M2.5
Wire Size AWG	N/A
Wire Size mm²	0.50-1.00
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	AA1-832-M2,5
Reference - Drawing Numbers	
Sales Drawing	SD-19324-001-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19324 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) Crimp Head for the AT-200 Pneumatic Hand Tool	640010100
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640050100
	640160036

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19324-0001](#)