

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0194180039](#)  
**Status:** **Active**  
**Overview:** [MX150L Industrial Sealed Connector System](#)  
**Description:** [MX150L 16 Circuit Receptacle for 14-16 AWG Wire, without CPA](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-19418-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-19417-001-001 (PDF)</a>	

**Agency Certification**

CSA	LR18689
UL	E152602

**General**

Product Family	Crimp Housings
Series	<a href="#">19418</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	<a href="#">MX150L Industrial Sealed Connector System</a>
Product Name	MX150L
UPC	822348526499

**Physical**

Circuits (maximum)	16
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	36.682/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

**Electrical**

Current - Maximum per Contact	18.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-19418-001-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19418-007-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - D(2020)4578-DC (25 June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19418](#) Series

**Mates With**

[19419](#) Plug, [19429](#) Panel Mount Plug

**Use With**

[19420](#) Female Crimp Terminal

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19418-0039](#)