


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0198032120](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: [Applicator Perishable Tool Kit](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207126
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ETC
Tool Type	Applicator
UPC	800753119390
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207126](#) Series

Application Tooling Description	FAQ Product #
Flag Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Metal Strip, Tab 6.35 x 0.81mm	190060004
Flag Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Metal Strip, Tab 4.75 x 0.51mm	190060007
Flag Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Metal Strip, Tab 4.75 x 0.81mm	190060010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19803-2120](#)