

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0198082025](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: ATP Perishable Tool Kit used in ATP Presses that Process Product on Tape

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Application Tooling
Series	207125
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Tool Type	Pneumatic Press
UPC	822350064958
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers	
Application Tooling Documents	ATS-198082025-001, TM-192280498-001, TM-192280498SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[207125](#) Series

Use With
MTA-105 Tape Applicator [192480050](#)
, Molex ATP-301 Air Crimping Press
[19228-0030](#)

Application Tooling Description	FAQ Product #
Perma-Seal Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	191640316
Perma-Seal Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	191640317
Perma-Seal Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Mylar Tape Carrier	191640318

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19808-2025](#)