

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [21039-0473](#)
Status: **Active**
Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers
Description: 1.00mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 30 Circuits, 0.127m Cable Length, 0.27mm Cable Thickness, Tin(Sn) Plating
Replacement Part Number: [15267-0473](#)

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-21039-001 \(PDF\)](#)

General
Product Family Cable
Series [21039](#)
Comments Contacts on the same side, Type A
Crimp Quality Equipment Yes
Overview [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Product Name Premo-Flex™ FFC Jumper
Replacement Part Number [15267-0473](#)
UPC 800754793032

Physical
Cable Length 0.127m
Circuits (Loaded) 30
Net Weight 3.701/g
Packaging Type Bag
Pitch - Termination Interface 1.00mm
Temperature Range - Operating -40°C to +80°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum per Contact 1.3A
Voltage - Maximum 30V

Solder Process Data
Duration at Max. Process Temperature (seconds) 30
Max. Cycles at Max. Process Temperature 1
Process Temperature max. C 250

Material Info

Reference - Drawing Numbers
Product Specification PS-21039-001
Sales Drawing SD-21039-001



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[21039Series](#)

Use With
www.molex.com/product/ffcfpc_th.html

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[21039-0473](#)