

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

21049-0314

Status:

Active

Overview:

Premo-Flex™ FFC and Etched Polyimide Jumpers

Description:

1.25mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 24 Circuits, 0.203m Cable Length, 0.27mm Cable Thickness, Tin(Sn) Plating

Replacement Part Number:

15268-0314



image - Reference only

Series

Documents:

- [Drawing \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)
- [Product Specification PS-21049-001 \(PDF\)](#)

General

Product Family	Cable
Series	21049
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ FFC and Etched Polyimide Jumpers
Product Name	Premo-Flex™ FFC Jumper
Replacement Part Number	15268-0314
UPC	800754821490

Physical

Cable Length	0.203m
Circuits (Loaded)	24
Packaging Type	Bag
Pitch - Termination Interface	1.25mm
Temperature Range - Operating	-40°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers

Product Specification	PS-21049-001
Sales Drawing	SD-21049-001

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
21049Series

Use With
www.molex.com/product/ffcfpc_th.html

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[21049-0314](#)