



– PLATING: SEE NOTE 2.
FOR ADDITIONAL INFORMATION SEE SDES-88.

CENTERLINE OF PIN IN AREA SHOWN
NOT TO VARY FROM CENTERLINE OF
PIN AT DATUM -E- BY MORE THAN
.005/(0.13) IN ANY DIRECTION



QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																											
 = 0  = 0  = 0  = 0  = 0  = 0  = 0  = 0  = 0		ADD ALT ENGRAVING VIEW EC NO: 111298 DRWN: MKIPPER CHK'D: MKIPPER REV APPR: FSMITH		2016/03/16 2017/04/11 2017/04/28		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS IN/MM		SCALE ---																			
<table border="1"> <tr> <td></td> <td>MM</td> <td>INCH</td> </tr> <tr> <td>4 PLACES</td> <td>±</td> <td>±</td> </tr> <tr> <td>3 PLACES</td> <td>±</td> <td>± .010</td> </tr> <tr> <td>2 PLACES</td> <td>± .025</td> <td>± .015</td> </tr> <tr> <td>1 PLACES</td> <td>± .036</td> <td>±</td> </tr> <tr> <td>0 PLACES</td> <td>±</td> <td>±</td> </tr> </table>					MM	INCH	4 PLACES	±	±	3 PLACES	±					± .010	2 PLACES	± .025	± .015	1 PLACES	± .036	±	0 PLACES	±	±	DRWN BY MKIPPER		DATE 2014/04/07	
	MM			INCH																									
4 PLACES	±			±																									
3 PLACES	±			± .010																									
2 PLACES	± .025	± .015																											
1 PLACES	± .036	±																											
0 PLACES	±	±																											
4 PLACES ± ± 3 PLACES ± ± .010 2 PLACES ± .025 ± .015 1 PLACES ± .036 ± 0 PLACES ± ±		CHK'D BY SAMIEC		DATE 98/10/09																									
ANGULAR TOL ± 1/2		APPR BY FSMITH		DATE 2014/08/06																									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE 		THIRD ANGLE PROJECTION		SERIES 7832		MATERIAL NUMBER SEE CHART		CUSTOMER GENERAL MARKET																			
U3		REV		C		DOCUMENT NUMBER SDA-7832		DOC TYPE PSD		DOC PART 000		SHEET NUMBER 1 OF 3																	

B

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

22-05-8162