


F




注記
NOTES:

1. 材料(MATERIAL)
ウェハー : ポリアミド, UL94V-0
WAFER: POLYAMIDE, UL94V-0
ピン: □0.635 黄銅
ニッケル下地:2micro-meter MIN. 金めっき :0.35micro-meter MIN.
PIN: □0.635 BRASS
NICKEL:2micro-meter MIN. Au PLATING:0.35micro-meter MIN.
△₂ 全極数が偶数の場合のみ適用。
APPLY FOR EVEN CIRCUITS PRODUCT ONLY.
3. 本図面はSD-5046-NAG REV-Fの再作成図面です。
THIS DOCUMENT HAS BEEN RE-DRAWING BASED ON SD-5046-NAG, REV-F.



E

D



C

基板取付穴推奨寸法
RECOMMENDED P.W.BOARD HOLE DIM.



29.5	27.5	22121122	5046-12AG	12
24.5	22.5	22121102	5046-10AG	10
22	20	22121092	5046-09AG	9
19.5	17.5	22121082	5046-08AG	8
17	15	22121072	5046-07AG	7
14.5	12.5	22121062	5046-06AG	6
12	10	22121052	5046-05AG	5
9.5	7.5	22121042	5046-04AG	4
7	5	22121032	5046-03AG	3
4.5	2.5	22121022	5046-02AG	2
(B)	(A)	ORDER NO.	ENG. NO.	CKT.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED&REDRAWING					
mm		5:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				molex KK 2.5 RIGHT ANGLE WAFER ASS'Y PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER50460001DOC TYPEPSDDOC PART000REVISIONA MATERIAL NUMBERSEE CHARTCUSTOMERGENERALSHEET NUMBER1 OF 1					
ANGULAR TOL ± °									
4 PLACES		±							
3 PLACES		±							
2 PLACES		± 0.2							
1 PLACE		± 0.2							
0 PLACES		± 0.2							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
						A3-SIZE		5046	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-12-1092](#)