

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0310671011

Status:

Active

Overview:

H-DAC 64 Unsealed Connector System

Description:

2.54mm H-DAC 64, 3 Way Receptacle Assembly, Single Row, Polarization B



|                                                               |                                                                  |
|---------------------------------------------------------------|------------------------------------------------------------------|
| Documents:                                                    |                                                                  |
| <a href="#">3D Model</a>                                      | <a href="#">Application Specification AS-31067-100-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                | <a href="#">Packaging Specification PK-30907-737-001 (PDF)</a>   |
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">Packaging Specification PK-31301-076-001 (PDF)</a>   |
| <a href="#">Product Specification PS-31100-0001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>             |

|                               |                                                    |
|-------------------------------|----------------------------------------------------|
| General                       |                                                    |
| Product Family                | Crimp Housings                                     |
| Series                        | 31067                                              |
| Application                   | Automotive, Power, Wire-to-Board, Wire-to-Wire     |
| Comments                      | Polarization Option B, Gray                        |
| Overview                      | <a href="#">H-DAC 64 Unsealed Connector System</a> |
| Product Name                  | H-DAC 64                                           |
| UPC                           | 800756477138                                       |
| Physical                      |                                                    |
| Circuits (maximum)            | 3                                                  |
| Color - Resin                 | Gray, White                                        |
| Gender                        | Receptacle                                         |
| Glow-Wire Capable             | No                                                 |
| Keying to Mating Part         | None                                               |
| Lock to Mating Part           | Yes                                                |
| Material - Resin              | Modified Polystyrene, Polyester                    |
| Net Weight                    | 1.100/g                                            |
| Number of Rows                | 1                                                  |
| Packaging Type                | Bag                                                |
| Panel Mount                   | No                                                 |
| Pitch - Mating Interface      | 2.54mm                                             |
| Pitch - Termination Interface | 2.54mm                                             |
| Polarized to Mating Part      | Yes                                                |
| Ports                         | 1                                                  |
| Stackable                     | No                                                 |
| Temperature Range - Operating | -40° to +100°C                                     |
| Electrical                    |                                                    |
| Current - Maximum per Contact | 11.0A, 9.0A                                        |
| Solder Process Data           |                                                    |
| Lead-freeProcess Capability   | N/A                                                |
| Material Info                 |                                                    |
| Reference - Drawing Numbers   |                                                    |
| Application Specification     | AS-31067-100-001                                   |
| Packaging Specification       | PK-30907-737-001, PK-31301-076-001                 |
| Product Specification         | PS-31100-0001-001                                  |
| Sales Drawing                 | SD-31109-003-001                                   |

EU ELV  
Compliant

EU RoHS  
Compliant

REACH SVHC  
Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

Halogen-Free  
Status  
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS  
ELV  
RoHS Phthalates

Green Image  
Compliant  
Not Contained

Search Parts in this Series

31067 Series

Mates With

H-DAC 64 3 Way Male Housing Assembly  
310671041 , 310671071

Use With

See Product Specification

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31067-1011](#)