

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0310681011](#)
Status: **Active**
Overview: [H-DAC 64 Unsealed Connector System](#)
Description: 2.54mm H-DAC 64, 4 Way Receptacle Assembly, Single Row, Polarization B

Documents:
[3D Model](#) [Application Specification AS-31067-100-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-30907-737-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-31301-076-001 \(PDF\)](#)
[Product Specification PS-31100-0001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Housings
Series [31068](#)
Application Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments Polarization Option B, Gray
Overview [H-DAC 64 Unsealed Connector System](#)
Product Name H-DAC 64
UPC 756054315187

Physical
Circuits (maximum) 4
Color - Resin Gray, White
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Modified Polystyrene, Polyester
Net Weight 1.385/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to Mating Part Yes
Ports 1
Stackable No
Temperature Range - Operating -40° to +100°C

Electrical
Current - Maximum per Contact 11.0A, 9.0A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Application Specification AS-31067-100-001
Packaging Specification PK-30907-737-001, PK-31301-076-001
Product Specification PS-31100-0001-001
Sales Drawing SD-31109-003-001



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[31068](#) Series

Mates With
HDAC 64, 4 Way Male Housing Assembly
[310681041](#) , [310681071](#) , [311000041](#) ,
[311010041](#)

Use With
See Product Specification

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[31068-1011](#)