

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0310681012](#)
Status: **Active**
Overview: [H-DAC 64 Unsealed Connector System](#)
Description: 2.54mm H-DAC 64, 4 Way Receptacle Assembly, Single Row, Polarization C

Documents:	
3D Model	Application Specification AS-31067-100-001 (PDF)
Drawing (PDF)	Packaging Specification PK-30907-737-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-076-001 (PDF)
Product Specification PS-31100-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	31068
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Polarization Option C, Brown
Overview	H-DAC 64 Unsealed Connector System
Product Name	H-DAC 64
UPC	756054393130

Physical	
Circuits (maximum)	4
Color - Resin	Brown (Carmel), White
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	1.385/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +100°C

Electrical	
Current - Maximum per Contact	11.0A, 9.0A

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-31067-100-001
Packaging Specification	PK-30907-737-001, PK-31301-076-001
Product Specification	PS-31100-0001-001
Sales Drawing	SD-31109-003-001



Series image - Reference only

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Contained Per -	
D(2021)4569-DC (8	
July 2021)	
Boric acid	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[31068](#) Series

Mates With
HDAC 64, 4 Way Male Housing Assembly
[310681042](#) , [310681072](#) , [311000042](#) ,
[311010042](#)

Use With
See Product Specification

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[31068-1012](#)