

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0330000004

Status:

Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Tin Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm², Right Reel Payoff

- Documents:
- Drawing (PDF)

Product Specification PS-33012-002-001 (PDF)

Application Specification AS-33000-001-001 (PDF)

Application Specification AS-33000-001-CH-001 (PDF)

Application Specification AS-33000-001-FR-001 (PDF)

Packaging Specification 313025040-000 (PDF)

Test Summary TS-33000-002-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	33000
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.
Crimp Quality Equipment	Yes
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	884982250543
Physical	
Gender	Male
Grip Code	M3
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.297/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.70mm max.
Wire Size AWG	N/A
Wire Size mm²	0.35-0.50

Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-33000-001-001, AS-33000-001-CH-001, AS-33000-001-FR-001
Packaging Specification	313025040-000
Product Specification	PS-33012-002-001
Sales Drawing	SD-33000-001-001
Test Summary	TS-33000-002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

33000 Series

Use With

33482 Dual Row Housing, 33481 Single Row Housing, 33486 Hybrid Housing

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Extraction Toolkit for MX150 Connectors	2002220700
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	638131500
Hand Crimp Tool for ISO (M3) Blade Terminals	638233600

This document was generated on 12/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[33000-0004](#) [33000-0004 \(Cut Strip\)](#) [33000-0004 \(Mouser Reel\)](#) [33000-0004 \(Loose Piece\)](#)