

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347360025](#)
Status: **Active**
Overview: MX64 Sealed Connectors
Description: 2.54mm Pitch MX64 Terminal, Silver Plating, 0.35mm², Left Reel Payoff, Also used with MX123 Female Receptacle Housing



Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-33468-001-001 \(PDF\)](#)
[Application Specification AS-33468-002-001 \(PDF\)](#)
[Packaging Specification 313025040-000 \(PDF\)](#)
[Packaging Specification PK-31302-480-001 \(PDF\)](#)
[Datasheet \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	34736
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff
Crimp Quality Equipment	Yes
Overview	MX64 Sealed Connectors
Product Name	MX123, MX64
UPC	884982893795
Physical	
Gender	Female
Material - Metal	Copper
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	0.329/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-2.06mm
Wire Size AWG	N/A
Wire Size mm²	0.35
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-33468-002-001
Packaging Specification	313025040-000, PK-31302-480-001
Product Specification	PS-33468-001-001
Sales Drawing	SD-33468-002-001

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[34736](#) Series

Use With
MX64 Sealed Single Row Crimp Housing [31403](#) , MX123 Female Receptacle Housing [34566](#) , [34576](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Tool for MX64 ISO Terminal	638258400
FineAdjust Applicator for MX64 ISO Terminal	639025100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[34736-0025](#) [34736-0025 \(Mouser Reel\)](#) [34736-0025 \(Cut Strip\)](#)