

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348240126

Status:

Active

Overview:

Description:

Mini50 Unsealed Receptacle, Dual Row, Non-Bridged, 12 Circuits, Polarization Option C, Dark Gray

General

Product Family	Crimp Housings
Series	34824
Application	Automotive, Power, Wire-to-Board
Overview	mini50_unsealed_connection_systems
Polarization	C
Product Name	Mini50
UPC	887191309484

Physical

Circuits (maximum)	12
Color - Resin	Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1.469/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020-001, AS-34791-020-CH-001, AS-34791-020-FR-001
Packaging Specification	PK-31301-538-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34824-002-001
Test Summary	347910020-TS-000

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
34824 Series

Mates With
Mini50 Vertical Headers [34825](#) , Mini50
Right-Angle Through Hole Header [34826](#) ,
Mini50 Right-Angle Surface Mount Header
[34897](#)

Use With
CTX50 Unsealed Terminals [560023](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34824-0126](#)