

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348258126

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Vertical Header, Dual Row, 12 Circuit, Polarization Option C, Dark Gray, Tape and Reel



Series image - Reference only

Documents:	
3D Model	Application Specification AS-34791-020-CH-001 (PDF)
3D Model (PDF)	Packaging Specification PK-47799-0001-001 (PDF)
Drawing (PDF)	Test Summary 347910020-TS-000 (PDF)
Product Specification PS-34791-020-001 (PDF)	Datasheet (PDF)
Application Specification AS-34791-020-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	34825
Application	Automotive, Power, Signal, Wire-to-Board
Overview	Mini50 Connection Systems
Product Name	Mini50
UPC	889056894135
Physical	
Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Gray (Dark)
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.200/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.87mm
PCB Locator	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	4.0A (for reference only)
Voltage - Maximum	14V (typical operating)
Material Info	
Reference - Drawing Numbers	

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34825 Series

Mates With

34824 Mini50 Unsealed Dual Row Receptacle

Application Specification	AS-34791-020-001, AS-34791-020-CH-001
Packaging Specification	PK-47799-0001-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34825-001-001
Test Summary	347910020-TS-000

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34825-8126](#)