

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0348269242

Status:


Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Right-Angle Header, Dual Row, 24 Circuit, Polarization Option C, 2.80mm Pin Length, Dark Gray, Tube



Series image - Reference only

- Documents:
- 3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification PS-34791-020-001 (PDF)

Application Specification AS-34791-020-001 (PDF)

Application Specification AS-34791-020-CH-001 (PDF)

Application Specification AS-34791-020-FR-001 (PDF)

Packaging Specification PK-31301-688-001 (PDF)

Test Summary 347910020-TS-000 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	34826
Application	Automotive, Power, Signal, Wire-to-Board
Overview	Mini50 Connection Systems
Product Name	Mini50
UPC	887191402789

Physical	
Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Gray (Dark)
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.965/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.80mm
PCB Locator	Yes
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	4.0A (for reference only)
Voltage - Maximum	14V (typical operating)

Material Info

Reference - Drawing Numbers

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

34826 Series

Mates With

Mini50 Unsealed Dual Row Receptacle
34824

Application Specification	AS-34791-020-001, AS-34791-020-CH-001, AS-34791-020-FR-001
Packaging Specification	PK-31301-688-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34826-001-001
Test Summary	347910020-TS-000

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34826-9242