

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348992071](#)
Status: **Active**
Overview:
Description: MXP120 Sealed Male Blade Connector with 7.00mm Clip-Slot, 2 Circuit, Yellow SIR Housing (T3-V2-S2 - 125°C on-engine vibration), Wire Dress Cover Interface Option 2, Key B

Application tooling part link	
Application Tooling Part Link	63824-6300
General	
Product Family	Crimp Housings
Series	34899
Application	Automotive, Safety, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	120mm_sealed_connection_system_
Polarization	B
Product Name	MXP120 Sealed
UPC	889056517812
Physical	
Circuits (maximum)	2
Color - Resin	Yellow
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	3.500/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	13.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-34900-0001-001
Packaging Specification	PK-31301-898-001
Sales Drawing	SD-34899-2001-001, SD-34899-6001-001

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[34899](#) Series

Mates With
MXP120 Female Receptacle [34900](#)

Use With
Tyco 1.2 MCON terminals
Or
Kostal
MLK 1.2 terminals

Application Tooling | **FAQ**
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Toolkit for MXP120 Sealed Connection System	638246300

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34899-2071