

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0349004116](#)  
**Status:** **Active**  
**Overview:** MXP120 Sealed Connector System  
**Description:** MXP120 Sealed Receptacle, 4 Circuit, Yellow SIR Housing with Long Shroud (T3-V2-S2 -125°C on-engine vibration), Key G, Light Gray Insert

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34900-0001-CH-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31301-898-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary TS-34900-0002-001 (PDF)</a>
<a href="#">Product Specification PS-34900-0001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-34900-0001-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**Application tooling part link**

Application Tooling Part Link 63824-6300

**General**

Product Family	Crimp Housings
Series	<a href="#">34900</a>
Application	Automotive, Safety, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	<a href="#">MXP120 Sealed Connector System</a>
Polarization	G
Product Name	MXP120 Sealed
UPC	889056197830

**Physical**

Circuits (maximum)	4
Color - Resin	Yellow
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	4.767/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

**Electrical**

Current - Maximum per Contact 13.0A

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-34900-0001-001, AS-34900-0001-CH-001
Packaging Specification	PK-31301-898-001
Product Specification	PS-34900-0001-001
Sales Drawing	SD-34899-6001-001, SD-34900-2001-001, SD-34900-6001-001
Test Summary	TS-34900-0002-001



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - D(2021)4569-DC (8 July 2021)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

[34900](#) Series

**Mates With**

MXP120 Male Blade Connector [34899](#)

**Use With**

MXP120 Backshell [1600914020](#) , [1600914120](#) , [1600914220](#) <br>MXP120 Cavity Plug [349961501](#) <br>MXP120 Cavity Plug Seal [349961902](#) <br>1.2 LL SWS from Tyco and Kostal

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Toolkit for MXP120 Sealed Connection System	<a href="#">638246300</a>
--	---------------------------

This document was generated on 10/04/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34900-4116](#)