

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349588342

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Vertical Hybrid Header, 3 Rows, 34 Circuits, Polarization Option C, Dark Gray, Tape and Reel

Documents:

- 3D Model

Application Specification AS-34959-001-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-31302-070-001 (PDF)
- 3D Model (PDF)

Packaging Specification PK-47799-0001-001 (PDF)
- Product Specification PS-34959-001-001 (PDF)

Datasheet (PDF)
- Application Specification 349590001-AS-CH-000 (PDF)

RoHS Certificate of Compliance (PDF)

General


Product Family	PCB Headers
Series	34958
Application	Automotive, Power, Signal, Wire-to-Board
Comments	30 x 0.50mm blades = 4.0A; 4 x 1.20mm blades = 16.0A
Overview	Mini50 Connection Systems
Product Name	Mini50
UPC	191128170307

Physical

Breakaway	No
Circuits (Loaded)	34
Circuits (maximum)	34
Color - Resin	Gray (Dark)
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	6.566/g
Number of Rows	3
Orientation	Vertical
PC Tail Length	3.07mm
PCB Locator	Yes
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	16.0A, 4.0A
Voltage - Maximum	500V DC



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

34958 Series

Mates With

Mini50 Unsealed Receptacle [349590342](#) , [349590349](#)

Material Info

Reference - Drawing Numbers

Application Specification	349590001-AS-CH-000, AS-34959-001-001
Packaging Specification	PK-31302-070-001, PK-47799-0001-001
Product Specification	PS-34959-001-001
Sales Drawing	SD-34958-300-001

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

34958-8342