

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0357680120

Status:

Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

.090mm Slip-on Receptacle Terminal

Documents:	
Drawing (PDF)	Packaging Specification PK-35768-002-001 (PDF)
Product Specification PS-68132-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	35768
Application	Power
Crimp Quality Equipment	Yes
Overview	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
UPC	756054263921
Physical	
Durability (mating cycles max)	50
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Net Weight	0.253/g
Packaging Type	Reel
Wire Insulation Diameter	2.30mm
Wire Size AWG	N/A
Wire Size mm²	0.30-0.50
Electrical	
Current - Maximum per Contact	10.0A
Material Info	
Reference - Drawing Numbers	
Crimp Specification	CS-35768-001-001
Packaging Specification	PK-35768-002-001
Product Specification	PS-68132-001-001
Sales Drawing	SD-35768-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

35768 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	638132700
Hand Crimp Tool for 2.28mm Slip-On Receptacle	638195200
FineAdjust for 2.30mm Slip-On Receptacle Terminal	639011800

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35768-0120](#)