

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0366380014

Status:

Active

Overview:

CMC and CMX Sealed, Hybrid, Modular Connectors

Description:

2.50mm, 3.50mm CMC Header, Right-Angle, 96 Position, 72 loaded, 2 Port, Black and Brown, Lead-Free



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-36638-001 (PDF)
3D Model (PDF)	Packaging Specification PK-36638-003 (PDF)
Drawing (PDF)	Datasheet (PDF)
Application Specification AS-36638-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	36638
Application	Automotive, Power, Wire-to-Board
Comments	Carton Box Packing
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	884982449930
Physical	
(p)ower-(s)ignal Configuration	12p - 60s
Breakaway	No
Circuits (Loaded)	72
Circuits (maximum)	96
Circuits Detail	12 x 1.5mm & 60 x 0.635mm terminals
Color - Resin	Black
Durability (mating cycles max)	20
First Mate / Last Break	Yes
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	No
Mated Height	6.70mm
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	116.886/g
Number of Rows	4
Orientation	Right Angle
PC Tail Length	2.90mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Carton
Pitch - Mating Interface	2.50mm, 3.50mm, 3.70mm
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Solder or Weld

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

36638 Series

Mates With

CMC Receptacle Connector [643201319](#) , [643203311](#)

Use With

CMC Receptacle Connector [643201319](#) , [643203311](#) , CMC CP Terminals [64322](#) , [64323](#) , CMC Blind Plug for CP Terminal [64325](#) , Wire Cap [643191201](#)

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-36638-001-001
Packaging Specification	PK-36638-001, PK-36638-003
Sales Drawing	SD-36638-001

This document was generated on 06/04/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[36638-0014](#)