

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0366480006

Status:

Active

Overview:

MLX Power Connectors

Description:

2.13mm Diameter MLX Power Crimp Housing Plug, Nylon, 94V-2, 9 Circuit, Black

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-42022-0001-001 (PDF)

Packaging Specification PK-42021-XX-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	36648
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current – Maximum per contact 20A if used with 36663 and 36664 terminal
Overview	MLX Power Connectors
Product Name	MLX
UPC	883906861520
Physical	
Circuits (maximum)	9
Color - Resin	Black
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	5.351/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C
Electrical	
Current - Maximum per Contact	13.5A, 20.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-42021-XX-001
Product Specification	PS-42022-0001-001
Sales Drawing	SD-42021-XX-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

36648 Series

Mates With

42002 MLX Power Connector Header,

42022 MLX Pin and Socket Receptacle,

43255 MLX Power Connector Header

Use With

MLX Crimp Terminal 36663 , 36664 , 42023

, 42024

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[36648-0006](#)