

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0367921201

Status:

Active

Overview:

MX120G Sealed Connectors

Description:

MX120G Pitch Sealed Female Connector Assembly, Dual Row 12 Circuit, Black



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-36783-001-001 (PDF)

Application Specification AS-36783-001-001 (PDF)

Packaging Specification PK-36783-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		Crimp Housings
Series		36792
Application		Wire-to-Board
Overview		MX120G Sealed Connectors
Product Name		MX120G
UPC		887191146799
Physical		
Circuits (maximum)		12
Color - Resin		Black
Flammability		94HB
Gender		Receptacle
Glow-Wire Capable		No
Keying to Mating Part		N/A
Lock to Mating Part		Yes
Material - Resin		Nylon
Net Weight		11.279/g
Number of Rows		2
Packaging Type		Carton
Panel Mount		No
Pitch - Mating Interface		3.20mm
Polarized to Mating Part		Yes
Stackable		No
Temperature Range - Operating		-40° to +105°C
Electrical		
Current - Maximum per Contact		10.5A
Solder Process Data		
Lead-freeProcess Capability		N/A

Material Info	
Reference - Drawing Numbers	
Application Specification	AS-36783-001-001
Packaging Specification	PK-36783-002-001
Product Specification	PS-36783-001-001
Sales Drawing	SD-36792-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

36792 Series

Use With

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[36792-1201](#)