

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0387406103

Status:

Active

Overview:

Beau Barrier Strips

Description:

11.11mm Pitch Beau PCB Fixed Mount Barrier Terminal Strip, Low Profile, 300V, 3 Circuits

Documents:

3D Model (PDF)

Drawing (PDF)

3D Model

Product Specification PS-38730-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

38740

N/A

One Piece

Beau Barrier Strips

Fixed Mount Barrier

Barrier Strip

800756319384

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Entry Angle

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length

PCB Retention

PCB Thickness - Recommended

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

3

3

Black

Horizontal

No

Brass

Tin

Tin

Polyester Alloy

1

Horizontal

5.50mm

Yes

2.40mm

No

11.11mm

11.11mm

No

No

-40° to +130°C

14, 16, 18, 20, 22

0.50-1.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

15.0A

300V

Solder Process Data

Lead-freeProcess Capability

WAVE

Material Info

Engineering Number

74503

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-38730-001-001

SD-38740-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Not Reviewed

Not Relevant

Not Reviewed

Search Parts in this Series

38740 Series

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38740-6103](#)