

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0391002112

Status:

Active

Overview:

Description:

10.00mm Pitch Beau Eurostyle Two-Screw Terminal Strips, 12 Circuits, Low Profile

General	
Product Family	Terminal Blocks
Series	39100
Application	Wire-to-Wire
Component Type	One Piece
Overview	eurostyle_twoscrew_barrier_strips
Product Name	Eurostyle Two Screw
Type	Barrier Strip
UPC	78172545211

Physical	
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	10.00mm
Pitch - Termination Interface	10.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	10, 12, 14, 16, 18

Electrical	
Current - Maximum per Contact	30.0A
Voltage - Maximum	300V

Material Info	
Engineering Number	M800-02-12-5

Reference - Drawing Numbers	
Sales Drawing	SD-39100-014-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39100-2112](#)