

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0391002512</u>
Status:	Active
Overview:	<u>Eurostyle Two-Screw Barrier Strips</u>
Description:	15.00mm Pitch Beau Eurostyle Two-Screw Terminal Strips, 12 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)



Series image - Reference only

General

Product Family	Terminal Blocks
Series	<u>39100</u>
Application	Wire-to-Wire
Component Type	One Piece
Overview	<u>Eurostyle Two-Screw Barrier Strips</u>
Product Name	Eurostyle Two Screw
Type	Barrier Strip
UPC	78172545268

Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	15.00mm
Pitch - Termination Interface	15.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	10, 12, 14, 6, 8

Electrical

Current - Maximum per Contact	63.0A
Voltage - Maximum	600V

Material Info

Engineering Number M800-04-12-5-M1

Reference - Drawing Numbers

Sales Drawing SD-39100-017-001

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39100-2512](#)