

NOTES:

1) MATERIAL:

HOUSING: "BLANK" = NYLON 6/6, UL94V-2, COLOR: NATURAL

"201" = NYLON 6/6, UL94V-0, COLOR: NATURAL

TERMINAL: C2700W BRASS

2) FINISH: 0.000003/(.0000001) MIN. TIN OVERALL OVER

0.000001/(.00000004) MIN. NICKEL OVERALL

3) PRODUCT SPECIFICATION: PS-3191-003


4) PACKAGING: PK-5219-002

5) MATES WITH: 3191-03R SERIES

DIFFERENCE OF DIMENSION IS INTENTIONAL TO PREVENT PART RISING FROM P.C.B.

7) PARTS CONFORM TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

ENG. NO.	ORDER NO.	PIN STYLE	HSG. MATERIAL	PIN PLATING
5219-03A	I5-31-I036	SOLID	94V-2 NYLON	TIN
5219-03B	I5-31-3036	HOLLOW	94V-2 NYLON	TIN
5219-03A-201	39-28-7038	SOLID	94V-0 NYLON	TIN

ADD P/N 15-31-3036 EC NO: UCP2014-1950 2013/12/16 DRWN: AELHAG 2013/12/16 CHKD: J.BELL 2013/12/19 APPR: FSMITH	REV N5	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	NEW INTERNATIONAL CONN. HEADER AND ASSY. MOLEX INCORPORATED SD-5219-03A-*	SHEET NO. 1 OF 1		
					mm	INCH	DRAWN BY	DATE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
				4 PLACES	± ---	± ---	TASAKAWA	1995/11/18							
				3 PLACES	± ---	± .005	CHECKED BY	DATE							
				2 PLACES	± 0.13	± .010	HHIRAMOT	1995/11/18							
				1 PLACE	± 0.25	± ---	APPROVED BY	DATE							
				ANGULAR ±1/2°			FUKUSHIM	1995/11/18							
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART								
							SIZE								
							C								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39-28-7038