

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0393710006

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

7.50mm Beau Eurostyle Pluggable PCB Terminal Block, 180° Wire Entry, 6 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39371

N/A

Plug

Eurostyle Terminal Blocks

Eurostyle Pluggable

Euro Block

822348040209

Physical

Circuits (Loaded)

Entry Angle

Flammability

Lock to Mating Part

Number of Rows

Orientation

PCB Retention

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

6

180° Angle

94V-0

None

1

Right Angle

N/A

No

7.50mm

7.50mm

Yes

Yes

110°C

12, 14, 16, 18, 20, 22, 24, 26, 28, 30

0.05-2.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

15.0A

300V

Material Info

Engineering Number

MX-CIF06003-0N

Reference - Drawing Numbers

Sales Drawing

SD-39371-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Not Relevant  |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

Search Parts in this Series  
39371 Series

Mates With  
39372 , 39373 Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39371-0006