

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0393710007](#)
Status: **Active**
Overview: [Eurostyle Terminal Blocks](#)
Description: 7.50mm Beau Eurostyle Pluggable PCB Terminal Block, 180° Wire Entry, 7 Circuits

Documents:
[3D Model](#) [3D Model \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E48521

General
Product Family Terminal Blocks
Series [39371](#)
Application N/A
Component Type Plug
Overview [Eurostyle Terminal Blocks](#)
Product Name Eurostyle Pluggable
Type Euro Block
UPC 822348040919

Physical
Circuits (Loaded) 7
Entry Angle 180° Angle
Flammability 94V-0
Lock to Mating Part None
Number of Rows 1
Orientation Right Angle
PCB Retention N/A
Panel Mount No
Pitch - Mating Interface 7.50mm
Pitch - Termination Interface 7.50mm
Polarized to Mating Part Yes
Stackable Yes
Temperature Range - Operating 110°C
Wire Size AWG 12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm² 0.05-2.50

Electrical
Current - Maximum per Contact 15.0A
Voltage - Maximum 300V

Material Info
Engineering Number MX-CIF07003-0N

Reference - Drawing Numbers
Sales Drawing SD-39371-001-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant with Exemption 6(c) REACH SVHC Contained Per - D(2021)4569-DC (8 July 2021) Lead Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS Not Relevant ELV Not Relevant RoHS Phthalates Not Contained
--	---

Search Parts in this Series
[39371](#) Series

Mates With
[39372](#) , [39373](#) Headers

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39371-0007](#)