

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0393740812

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

7.50mm Beau Eurostyle Pluggable PCB Terminal Block, 90° Wire Entry, 12 Circuits

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

39374

Application

N/A

Component Type

Plug

Overview

Eurostyle Terminal Blocks

Product Name

Eurostyle Pluggable

Type

Euro Block

UPC

822348050567

Physical

Circuits (Loaded)

12

Entry Angle

90° Angle

Flammability

94V-0

Lock to Mating Part

None

Number of Rows

1

Orientation

Vertical

PCB Retention

N/A

Panel Mount

No

Pitch - Mating Interface

7.50mm

Pitch - Termination Interface

7.50mm

Polarized to Mating Part

Yes

Stackable

Yes

Temperature Range - Operating

110°C

Wire Size AWG

12, 14, 16, 18, 20, 22, 24, 26, 28, 30

Wire Size mm²

0.05-2.50

Electrical

Current - Maximum per Contact

15.0A

Voltage - Maximum

300V

Material Info

Engineering Number

MX-CVF120L3-0N

Reference - Drawing Numbers

Sales Drawing

SD-39374-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

39374 Series

Mates With

39372 , 39373 Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39374-0812](#)