

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0393740905

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

7.50mm Beau Eurostyle Pluggable PCB Terminal Block, 270° Wire Entry, 5 Circuits

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E48521
General	
Product Family	Terminal Blocks
Series	39374
Application	N/A
Component Type	Plug
Overview	Eurostyle Terminal Blocks
Product Name	Eurostyle Pluggable
Type	Euro Block
UPC	822348047383
Physical	
Circuits (Loaded)	5
Entry Angle	270° Angle
Flammability	94V-0
Lock to Mating Part	None
Number of Rows	1
Orientation	Vertical
PCB Retention	N/A
Panel Mount	No
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm²	0.05-2.50
Electrical	
Current - Maximum per Contact	15.0A
Voltage - Maximum	300V
Material Info	
Engineering Number	MX-CVF050R3-0N
Reference - Drawing Numbers	
Sales Drawing	SD-39374-002



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

39374 Series

Mates With

39372 , 39373 Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39374-0905