

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395005008

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.50mm Pitch Eurostyle Horizontal Plug, Green Housing, 8 Circuits

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-39500-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39500

N/A

Plug

Eurostyle Terminal Blocks

ESE, Eurostyle Pluggable

Euro Block

822350427296

Physical

Circuits (Loaded)

Entry Angle

Lock to Mating Part

Net Weight

Number of Rows

Orientation

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

8

Vertical

None

18.000/g

1

Horizontal

No

3.50mm

3.50mm

Yes

No

-40° to +105°C

16, 18, 20, 22, 24, 30

0.05-1.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

8.0A

300V

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-39500-001-001

SD-39500-001-001, SD-39500-001-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Relevant

Not Reviewed

Search Parts in this Series

39500 Series

Mates With

39501

Vertical PCB Header,

39502

Horizontal PCB Header, Most 3.50mm Pitch

Industry Standard PCB Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39500-5008](#)