

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395016520

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.50mm Pitch Eurostyle Vertical PCB Header, Green Housing, Gold (Au) Plated, 20 Circuits



Series image - Reference only

Documents:

- 3D Model

Product Specification PS-39500-001-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Drawing (PDF)

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

39501

Application

N/A

Component Type

PCB Header

Overview

Eurostyle Terminal Blocks

Product Name

ESE, Eurostyle Pluggable

Type

Euro Block

UPC

822350433860

Physical

Circuits (Loaded)

20

Entry Angle

N/A

Lock to Mating Part

None

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.50mm

PCB Thickness - Recommended

2.50mm

Panel Mount

No

Pitch - Mating Interface

3.50mm

Pitch - Termination Interface

3.50mm

Polarized to Mating Part

Yes

Shrouded

Fully

Stackable

No

Temperature Range - Operating

-40° to +105°C

Wire Size AWG

N/A

Electrical

Current - Maximum per Contact

8.0A

Voltage - Maximum

300V

Material Info

Reference - Drawing Numbers

Product Specification

PS-39500-001-001

Sales Drawing

SD-39501-001-001, SD-39501-002

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

39501 Series

Mates With

Most 3.50mm Pitch Industry Standard Plugs, 39500 Horizontal Plug, 39503 Vertical Plug

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39501-6520](#)