

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395021002

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.50mm Pitch Eurostyle Horizontal PCB Header, 2 Circuits

Documents:

- 3D Model (PDF)

Product Specification PS-39500-001-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- 3D Model

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

39502

Application

N/A

Component Type

PCB Header

Overview

Eurostyle Terminal Blocks

Product Name

ESE, Eurostyle Pluggable

Type

Euro Block

UPC

822350434751

Physical

Circuits (Loaded)

2

Entry Angle

N/A

Lock to Mating Part

None

Number of Rows

1

Orientation

Horizontal

PC Tail Length

3.50mm

PCB Thickness - Recommended

2.50mm

Panel Mount

No

Pitch - Mating Interface

3.50mm

Pitch - Termination Interface

3.50mm

Polarized to Mating Part

Yes

Shrouded

Fully

Stackable

No

Temperature Range - Operating

-40° to +105°C

Wire Size AWG

N/A

Electrical

Current - Maximum per Contact

8.0A

Voltage - Maximum

300V

Material Info

Reference - Drawing Numbers

Product Specification

PS-39500-001-001

Sales Drawing

SD-39501-002-001, SD-39502-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39502 Series

Mates With

Most 3.50mm Pitch Industry Standard Plugs,
39500 Horizontal Plug, 39503 Vertical Plug

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[39502-1002](#)