

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395037004

Status:

Active

Overview:

[Eurostyle Terminal Blocks](#)

Description:

3.50mm Pitch Eurostyle Vertical Plug, Rear Wire Entry, Green Housing, 4 Circuits



Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-39500-001-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification		
UL		E48521
General		
Product Family		Terminal Blocks
Series		39503
Application		N/A
Comments		Rear Wire Entry
Component Type		Plug
Overview		Eurostyle Terminal Blocks
Product Name		ESE, Eurostyle Pluggable
Type		Euro Block
UPC		822350679794
Physical		
Circuits (Loaded)		4
Entry Angle		Horizontal
Lock to Mating Part		None
Number of Rows		1
Orientation		Vertical
Panel Mount		No
Pitch - Mating Interface		3.50mm
Pitch - Termination Interface		3.50mm
Polarized to Mating Part		Yes
Stackable		No
Temperature Range - Operating		-40° to +105°C
Wire Size AWG		16, 18, 20, 22, 24
Wire Size mm²		0.20-1.31
Electrical		
Current - Maximum per Contact		8.0A
Voltage - Maximum		300V
Material Info		
Reference - Drawing Numbers		
Product Specification		PS-39500-001-001
Sales Drawing		SD-39503-002

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[39503](#) Series

Mates With

[39501](#) Vertical PCB Header, [39502](#) Horizontal PCB Header, Most 3.50mm Pitch Industry Standard PCB Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39503-7004](#)