

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395100005

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

3.81mm Pitch Eurostyle Horizontal Plug, 5 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-39500-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39510

N/A

Plug

Eurostyle Terminal Blocks

ESE, Eurostyle Pluggable

Euro Block

822350686648

Physical

Circuits (Loaded)

Entry Angle

Lock to Mating Part

Number of Rows

Orientation

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Wire Size AWG

Wire Size mm²

5

Vertical

None

1

Horizontal

No

3.81mm

3.81mm

Yes

No

-40° to +105°C

16, 18, 20, 22, 24

0.20-1.31

Electrical

Current - Maximum per Contact

Voltage - Maximum

8.0A

300V

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-39500-001-001

SD-39510-001-001, SD-39510-001-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

39510 Series

Mates With

Most 3.81mm Pitch Industry Standard PCB Headers, 39511 Vertical PCB Header, 39512 Horizontal PCB Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[39510-0005](#)