

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395232807

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.00mm Pitch Eurostyle Vertical Plug, with Standard Imprinting, Rear Wire Entry, Gold (Au) Plated, 7 Circuits



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-39500-001-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

|                               |                                          |
|-------------------------------|------------------------------------------|
| General                       |                                          |
| Product Family                | Terminal Blocks                          |
| Series                        | 39523                                    |
| Application                   | N/A                                      |
| Comments                      | Rear Wire Entry with Standard Imprinting |
| Component Type                | Plug                                     |
| Overview                      | Eurostyle Terminal Blocks                |
| Product Name                  | ESE, Eurostyle Pluggable                 |
| Type                          | Euro Block                               |
| UPC                           | 822350467377                             |
| Physical                      |                                          |
| Circuits (Loaded)             | 7                                        |
| Entry Angle                   | Horizontal                               |
| Lock to Mating Part           | Yes                                      |
| Number of Rows                | 1                                        |
| Orientation                   | Vertical                                 |
| Panel Mount                   | No                                       |
| Pitch - Mating Interface      | 5.00mm                                   |
| Pitch - Termination Interface | 5.00mm                                   |
| Polarized to Mating Part      | Yes                                      |
| Stackable                     | No                                       |
| Temperature Range - Operating | -40° to +105°C                           |
| Wire Size AWG                 | 12, 14, 16, 18, 20, 22, 24, 26           |
| Wire Size mm²                 | 0.13-3.31                                |
| Electrical                    |                                          |
| Current - Maximum per Contact | 18.0A                                    |
| Voltage - Maximum             | 300V                                     |
| Solder Process Data           |                                          |
| Lead-freeProcess Capability   | N/A                                      |
| Material Info                 |                                          |
| Reference - Drawing Numbers   |                                          |
| Product Specification         | PS-39500-001-001                         |
| Sales Drawing                 | RSD-39523-001, SD-39523-002              |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Reviewed                                                  |              |
| REACH SVHC                                                    |              |
| Not Reviewed                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Reviewed                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Reviewed |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Reviewed |

Search Parts in this Series

39523 Series

Mates With

39521 Vertical PCB Header, 39522 Horizontal PCB Header, Most 5.00mm Pitch Industry Standard PCB Headers, 39528 Dual Level PCB Header, Open Ends

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39523-2807](#)