

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0395321009
Status: Active
Overview: Eurostyle Terminal Blocks
Description: 5.08mm Pitch Eurostyle Horizontal PCB Header, 9 Circuits

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-39500-001-001 \(PDF\)](#)
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[3D Model \(PDF\)](#)

Agency Certification
UL E48521

General
Product Family Terminal Blocks
Series 39532
Application N/A
Component Type PCB Header
Overview Eurostyle Terminal Blocks
Product Name ESE, Eurostyle Pluggable
Type Euro Block
UPC 822350506601

Physical
Circuits (Loaded) 9
Entry Angle N/A
Lock to Mating Part Yes
Number of Rows 1
Orientation Horizontal
PC Tail Length 5.08mm
PCB Thickness - Recommended 3.18mm
Panel Mount No
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Polarized to Mating Part Yes
Shrouded Closed Ends
Stackable No
Surface Mount Compatible (SMC) N/A
Temperature Range - Operating -40° to +105°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 15.0A
Voltage - Maximum 300V

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Product Specification PS-39500-001-001
Sales Drawing SD-39532-002-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
39532 Series

Mates With
39530 Horizontal Plug, 39533 Vertical Plug,
Most 5.08mm Pitch Industry Standard Plugs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[39532-1009](#)