

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0395332003](#)
Status: **Active**
Overview: [Eurostyle Terminal Blocks](#)
Description: 5.08mm Pitch Eurostyle Vertical Plug, Rear Wire Entry, 3 Circuits

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-39500-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[3D Model](#)

Agency Certification
UL E48521

General
Product Family Terminal Blocks
Series [39533](#)
Application N/A
Comments Rear Wire Entry
Component Type Plug
Overview [Eurostyle Terminal Blocks](#)
Product Name ESE, Eurostyle Pluggable
Type Euro Block
UPC 822350523141

Physical
Circuits (Loaded) 3
Entry Angle Horizontal
Lock to Mating Part Yes
Number of Rows 1
Orientation Vertical
Panel Mount No
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C
Wire Size AWG 12, 14, 16, 18, 20, 22, 24, 26
Wire Size mm² 0.13-3.31

Electrical
Current - Maximum per Contact 18.0A
Voltage - Maximum 300V

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Product Specification PS-39500-001-001
Sales Drawing SD-39533-002-001, SD-39533-002-002



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant with Exemption 6(c)
REACH SVHC
Contained Per -
D(2021)4569-DC (8
July 2021)
Lead
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS 50 Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[39533](#) Series

Mates With
[39531](#) Vertical PCB Header, [39532](#)
Horizontal PCB Header, Most 5.08mm Pitch
Industry Standard PCB Headers, [39538](#)
Dual Level Header, Open Ends

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39533-2003](#)