

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395337924

Status:

Active

Overview:

Description:

5.08mm Pitch Eurostyle Vertical Plug, with Reverse Imprinting, Rear Wire Entry, Green Housing, Gold (Au) Plated, 24 Circuits

|                               |                                         |
|-------------------------------|-----------------------------------------|
| Agency Certification          |                                         |
| UL                            | E48521                                  |
| General                       |                                         |
| Product Family                | Terminal Blocks                         |
| Series                        | 39533                                   |
| Application                   | N/A                                     |
| Comments                      | Rear Wire Entry with Reverse Imprinting |
| Component Type                | Plug                                    |
| Overview                      | eurostyle_terminal_blocks               |
| Product Name                  | ESE, Eurostyle Pluggable                |
| Type                          | Euro Block                              |
| UPC                           | 822350533966                            |
| Physical                      |                                         |
| Circuits (Loaded)             | 24                                      |
| Entry Angle                   | Horizontal                              |
| Lock to Mating Part           | Yes                                     |
| Number of Rows                | 1                                       |
| Orientation                   | Vertical                                |
| Panel Mount                   | No                                      |
| Pitch - Mating Interface      | 5.08mm                                  |
| Pitch - Termination Interface | 5.08mm                                  |
| Polarized to Mating Part      | Yes                                     |
| Stackable                     | No                                      |
| Temperature Range - Operating | -40° to +105°C                          |
| Wire Size AWG                 | 12, 14, 16, 18, 20, 22, 24, 26          |
| Wire Size mm²                 | 0.13-3.31                               |
| Electrical                    |                                         |
| Current - Maximum per Contact | 18.0A                                   |
| Voltage - Maximum             | 300V                                    |
| Solder Process Data           |                                         |
| Lead-freeProcess Capability   | N/A                                     |
| Material Info                 |                                         |
| Reference - Drawing Numbers   |                                         |
| Product Specification         | PS-39500-001-001                        |
| Sales Drawing                 | SD-39533-002                            |

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

39533 Series

Mates With

39531 Vertical PCB Header, 39532 Horizontal PCB Header, Most 5.08mm Pitch Industry Standard PCB Headers, 39538 Dual Level Header, Open Ends

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39533-7924